

AlteTube™

Screw cap tubes in SBS rack format



	0.5ml Screw cap	0.75ml Screw cap	1.1ml Screw cap	1.4ml Screw cap
Thread type	Internal	Internal	Internal	Internal
Max working volume - ml	0.3	0.49	0.75	0.92
Min storage temperature - °C	-196	-196	-196	-196
Tube height - mm	20	27	36.5	44
Tube height with cap - mm	27	34	43.5	51
Inner diameter - mm	6.8	6.8	6.8	6.8
Outer diameter with cap - mm	8.4	8.4	8.4	8.4
Pitch - mm	9.0	9.0	9.0	9.0
Identification	2D DataMatrix barcode on base			
2D DataMatrix barcode	White on black, 3mm x 3mm, 2 alpha prefix (AL) and 8 numeric Custom prefix available / Black on white available			
Capping options	Screw caps			
Sterility options	AlteClean™ / Sterile (E-beam) / Ethylene oxide (EtO) on request			
Rack format	8 x 12 - SBS (96 tubes)			
Rack material	Polypropylene base with polycarbonate lid			
Rack height with lid - mm	31	37	50	55.5
Packaging options	Bulk packed tubes, no cap – 960/case Bulk packed tubes, precapped – 960/case Racked tubes, no cap – 96/rack, 10 racks/case Racked tubes, precapped – 96/rack, 10 racks/case Bulk screw caps – 960/case Empty racks – 10 racks/case			



TO LEARN MORE, PLEASE CONTACT
ROB OSBORN AT 508.395.8161
OR ROSBORN@AUTOGEN.COM

Maximum working volumes are for guidance only.

Please request samples for evaluation.

Warning: Caps should not be immersed in Liquid Nitrogen.

AlteTubes should be stored in gas phase Liquid Nitrogen (GPLN) only.